UltraSOLV[®] 1700 Series Swabs

Description

UltraSOLV[®] 1700 Series Swabs are excellent general purpose cleaning tools for HDD components, optics, medical devices or vacuum equipment. UltraSOLV® tip construction provides good particle and residue removal with a minimum of particle transfer due to abrasion. Unique thermal bonding and cleaning process ensure a minimum of particle shedding from foam seal.

cleaning critical surfaces

Advantages

- Excellent absorbency and fiber free construction make it a perfect replacement for cotton swabs.
- High strength and abrasion resistance of UltraSOLV® foam tip minimizes particle shedding due to abrasion, common with standard foam and cotton swabs (See pictures at right).
- Extremely low ionic and NVR levels for HDD and optic cleaning applications.
- W Unique thermal bonding process ensures no adhesive residue and minimizes particle generation from seal.
- Available in a variety of tip sizes for cleaning small hard-to-access components, o-ring grooves, and corners.
- 🔮 ESD safe tip

Cleanliness

Particles: Less than 2000, $.5\mu$ to 25μ particles per swab

TNVR's: mg / swab

NVR (DI Water) < 0.15 NVR (IPA) < 0.40

lonics: µg/swab



| Chloride | < 0.90 | Magnesium | < 0.02 |
|----------|--------|-----------|--------|
| Sodium | < 0.2 | Sulfate | < 0.06 |
| Fluoride | N/D | Nitrate | N/D |
| Bromide | N/D | Potassium | < 0.02 |



UltraSOLV® Tip Out-of-the Bag



Competitor A Out-of-the Bag



Competitor B Out-of-the Bag



UltraSOLV® Tip After HSA Swabbing



Comp. A After HSA Swabbing



Comp. B After HSA . Swabbing

USA +1.760.599.7160 fax +1.760.599.7322 Thailand +66.35740717 fax +66.35740744

Swab Models

Measured in Millimeters. ± 0.02

| Product Name | HT1700 | HT1701 | HT1702 | HT1712 | HT1716 | HT1729 | HT1730 | HT1732 | HT1748 | HT1750 | HT1790 |
|--------------------|----------------|------------------|---------------------------|-----------------|----------|--------------------|-----------------------------|----------------|-------------------------|------------------------------|-----------------------------------|
| | 9 | | | | | | | | | | 7 |
| Head Material | UltraSOLV®Foam | | | | | | | | | | |
| Head Thickness | 7.0 | 5.0 | 3.10 | 6.2 | 7.5 | 2.9 | 2.2 | 3.6 | 3.4 | 2.6 | 6.6 7.11 |
| Head Width | 11.0 | 6.0 | 3.20 | 5.2 | 6.9 | 3.8 | 3.7 | 3.6 | 3.4 | 2.6 | 12.7 7.11 |
| Head Length | 20.8 | 18.0 | 10.30 | 13.8 | 21.0 | 10.0 | 9.2 | 11.0 | 17.3 | 10.5 | 14.22 16.76 |
| Handle Material | Polypropylene | | | | | | | | | | |
| Handle Diameter | 2.9 | 2.9 | 2.5 | 3.1 | 4.3 | 2.5 | 2.5 | 2.5 | 2.5 | 2.5 | 5.58 |
| Handle Length | 121.7 | 132.5 | 58.0 | 293.4 | 303 | 58.7 | 59 | 57.5 | 65.1 | 58.4 | 160.02 |
| Total length | 142.5 | 150.5 | 68.5 | 307.2 | 324 | 68.7 | 68.2 | 68.5 | 82.4 | 68.9 | 176.78 |
| Head Bond | Thermal | | | | | | | | | | |
| Handle Color | Blue | | | | | | Black | | | | |
| Description | Rigid Oval | Flexible Oval | Semi- Flexible Bulb | Rigid, Round | Flexible | Flexible Paddle | Thin, Flexible Paddle | Rigid Round | Rigid, Long Spear | Flexible Spear Pointed | Dual Tip: Angled & Lollipop |

Available Packaging

| <u>Tip Style</u> | 5 Swabs/Bag | 50 Swabs/Bag | 100 Swabs/Bag | 500 Swabs/Bag |
|------------------|-------------|--------------|---------------|---------------|
| HT1700 | HT1700-5 | | | HT1700-500 |
| HT1701 | HT1701-5 | | | HT1701-500 |
| HT1702 | HT1702-5 | HT1702-50 | | HT1702-500 |
| HT1712 | | | HT1712-100 | |
| HT1716 | HT1716-5 | HT1716-50 | | |
| HT1729 | HT1729-5 | HT1729-50 | | HT1729-500 |
| HT1730 | | | | HT1730-500 |
| HT1732 | HT1732-5 | HT1732-50 | | HT1732-500 |
| HT1748 | HT1748-5 | HT1748-50 | | HT1748-500 |
| HT1750 | HT1750-5 | HT1750-50 | | HT1750-500 |
| HT1790 | | HT1790-50 | | |

FOR TECHNICAL SUPPORT AND SITE TRAINING: Please contact our technical assistance services at 760.599.7160 or e-mail: info@foamtecintlwcc.com and our staff will arrange for a technical service engineer or a field sales engineer to assist you.