

BioClean Clearview™

Autoclavable
Cleanroom
Goggles

“OPTICALLY CORRECT
FOR CLEAR VISION”

Super-soft silicone rubber
provides unrivalled comfort

Indirect
ventilation system

Tested to over
40 autoclave cycles

Can be comfortably
worn over eye glasses

Anti-scratch
polycarbonate lens

Processed to ensure
ISO Class 4 compatibility

MASTER CODE

SPECIFICATIONS

PACKAGING

BCAH

Silicone rubber body
Polycarbonate lens
Non-linting head band
ISO Class 4 & EU GMP Grade A compatible

One piece per PE bag
12 pieces per box
Packing 12 x 5 (60 pieces) per carton



GB10/81851



GB04/61092

UK e-mail: info@nitritex.com
Tel: +44 (0) 1638 663338
Fax: +44 (0) 1638 668890
Nitritex Ltd, CB8 7YY, United Kingdom

 Nitritex
www.nitritex.com


MASTER CODE

BCAH

RE-ORDER CODE SIZE

BCAH Universal

PRODUCT ILLUSTRATION



Clear

DESIGN: Light weight silicone rubber body.
Anti-scratch polycarbonate lens.

OTHER FEATURES: Indirect ventilation.

STERILIZATION METHOD: Autoclave at 121°C.

QUALITY SYSTEMS: Manufactured in a facility holding ISO 9001:2008 registration and packed in a NEBB Certified ISO Class 4 (Class 10) cleanroom.

SAMPLING AND INSPECTION: 100% inspection.

STORAGE INSTRUCTIONS: Store in a dry, cool place (<40°C) away from direct sunlight and fluorescent light.

LOT NUMBER: This is shown on the inner box and the outer carton to provide product traceability.

PACKAGING SPECIFICATION: One piece per PE bag (Remove bag prior to autoclaving);
12 pieces per inner box;
Five boxes per carton (60 pieces).