



# BioClean Excell™

## STERILE HAND-SPECIFIC NITRILE CLEANROOM GLOVES

BEXS



**BioClean Excell™** sterile powderfree nitrile hand-specific cleanroom gloves are totally latex-free eliminating Type 1 allergic reactions associated with natural rubber latex gloves. As they are accelerator and sulphur free, they also virtually eliminate Type 4 allergies. They are resistant to a wide range of chemicals and are more puncture resistant than natural latex gloves.

Individually packed in an inner wallet within an 'Easy Tear'™ PE bag, BioClean Excell™ are suitable for use in ISO Class 4 and EU GMP Grade A compatible cleanrooms.

They have a beaded cuff for added strength, easier donning and a secure fit at the arm and are 300mm (12") length for added protection in the cuff area. Anatomically shaped for improved comfort and to reduce wearer fatigue they have extremely low levels of chlorides and extractable metals.

These gloves are available in a range of sizes to suit all users and comply to the European PPE Category 3 Complex Design.



*"Sterile with No Latex, Accelerators or Sulphur!"*

|                             |                        |                               |
|-----------------------------|------------------------|-------------------------------|
| NITRITEX LTD.               | T: +44 (0) 1638 663338 | E: info@nitritex.com          |
| NITRITEX ASIA PTE LTD.      | T: +65 6536 9123       | E: nitritex@pacific.net.sg    |
| NITRITEX PUERTO RICO Inc.   | T: +1 787 232 5084     | E: info@nitritex.com.pr       |
| NITRITEX CANADA LTD.        | T: +1 (905) 946 9539   | E: info@nitritexcanada.com    |
| NITRITEX MALAYSIA Sdn. Bhd. | T: +(603) 3122 2614    | E: operations@nitritex.com.my |





# BioClean Excell™

## STERILE HAND-SPECIFIC NITRILE CLEANROOM GLOVES

### BEXS

|                            |   |
|----------------------------|---|
| Colour:                    | Natural.  |
| Length:                    | 300mm (12").  |
| Material:                  | Nitrile.  |
| Type:                      | Hand specific.  |
| Surface:                   | Micro-textured.   |
| Other Features:            | Powderfree, anatomical shape, beaded cuff.  |
| Protein Level:             | Zero. Nitrile contains no natural latex proteins.   |
| Sterilisation Method:      | Gamma irradiation.  |
| Packing:                   | Bagged  |
| AQL:                       | 1.5 for holes (1000ml water test).  |
| Particulates:              | Processed in a cleanroom environment to ensure compatibility with ISO Class 4 & EU GMP Grade A operating conditions.  |
| Extractables:              | Extended leaching in pure de-ionised water ensures low levels of chlorides and extractable metals.  |
| Physical Properties:       | Manufactured to exceed the requirements of the PPE Gloves Standard EN420:2003 and the European Medical Gloves Standard EN455 (Parts 1, 2 & 3).  |
| Quality Systems:           | Manufactured in a facility holding ISO 9001:2000 and 89/686/EEC Article 11b certifications.   |
| Sampling & Inspection:     | In accordance with ISO 2859.  |
| Storage Instructions:      | Store in a dry, cool place (<40°C) away from direct sunlight and fluorescent light.   |
| Shelf Life:                | Five (5) years from date of manufacture.  |
| Bar Codes:                 | Each size carries a unique bar code on the carton (ITF-14). This allows automatic data entry into Stock Control Systems.  |
| Lot Number:                | This is shown on the sealed pouch and outer carton to provide product traceability.   |
| Packaging:                 | One cuffed pair per inner plastic wallet;<br>One inner wallet per 'Easy Tear' PE bag;<br>10 pairs per sealed outer PE bag;<br>20 outer bags per carton liner;<br>One carton liner per carton (200 pairs). |
| Compatibility:             | ISO Class 4 & EU GMP Grade A.   |
| Regulatory Classification: | Category 3 - Complex Design Personal Protective Equipment conforming to EN420:2003 & EN374-1 & 2:2003.  |
| Product Codes and Sizes:   | BEXS-60: 6.0<br>BEXS-65: 6.5<br>BEXS-70: 7.0<br>BEXS-75: 7.5<br>BEXS-80: 8.0<br>BEXS-85: 8.5<br>BEXS-90: 9.0<br>BEXS-100: 10.0  |

*"Sterile with No Latex, Accelerators or Sulphur!"*

BEXS/PDSZ



GB04/61092

