
OVERLIGHT

OTG

OVERLIGHT is the new generation of OTG (over the glasses). Highly wrap-around and attractive, they guarantee maximum safety for all, including wearers of prescription glasses.



- # HIGHLY WRAP-AROUND FRAME
- **SIDE, UPPER AND LOWER PROTECTION**
- **DESIGN**



OVERLIGHT

OTG

MODEL	VERSIONS	REFERENCES	LENS MARKING	FRAME MARKING	COATINGS
OVERLIGHT	Clear	OVLITLPSI	2C-1,2 😭 1 FT C€	₩ EN166 FT C€	Anti-scratch/anti-fog

LENS MARKING

Optical class symbols:

1. Continuous work

Mechanical strength symbols:

- F. Low energy impact, resists a 6 mm, 0.86 g ball at 45 m/s Maximum protection for glasses.
- T. The letter T, immediately after the mechanical strength symbol. authorises use for high speed particles at extreme temperatures.

Others symbols:

€ European standard Manufacturer name

PACKAGING A	AND EAN13 CODE	
	OVLITLPSI	
Individual plastic bag	3660740006495	
0 safety spectacles per box	3660740106492	
180 safety spectacles per outer pack	3660740206499	









FRAME MARKING

EN 166: guaranteed minimum resistance of the protective eyewear against everyday risks including dropping the protective eyewear onto the ground, ageing by light exposure, exposure to heat or corrosion etc.

- F. Low energy impact, resists a 6 mm, 0.86 g ball at 45 m/s Maximum protection for glasses.
- T. The letter T, immediately after the mechanical strength symbol, authorises use for high speed particles at extreme temperatures.

Bollé Safety product approval certificates to CE standards will be sent on request.

CLEANING AND STORAGE

CLEANING: The lenses should be cleaned regularly. Bollé Safety recommends only using the B-clean lens cleaning system.

MAINTENANCE: Pitted, scratched or damaged lenses must be replaced by replacing the complete product. If the frame is damaged also replace the complete product. After each use it is recommended to keep the spectacles or goggles in a microfiber pouch or rigid case.

STORAGE: All products must be stored in a dry and clean environment.

CHA	ARACTERISTICS	
LENSES	PC - 2,4 mm - Curve 2.75	
FRAME	PC	
TEMPLES	PC	
STRAP	Non applicable	
FOAM	Non applicable	
SPARE LENSES	No	

02/05/2016

