# COVERALL CLEAN & AUTOCLAVE

## FOR «CLEAN ROOMS»

The COVERALL CLEAN & AUTOCLAVE goggles have been especially developed to guarantee high protection & comfort in risky environments, like pharmaceutics, micro-electronics or even surgery departments.





COVACLAVE



79 g

#### // COVACLAVE

- 🛨 CLEAN NEOPRENE STRAP
- OVERFLOW CHUTE FOR LIQUIDS
- FITS OVER PRESCRIPTION SPECTACLES
- TPR FRAME / UPPER INDIRECT VENTILATION / SEALED IN THE LOWER PART
- HIGH-COMFORT AUTOCLAVABLE GOGGLE
- + ♦PLATINUM COATING (+P)



COVACLEAN



90 g

#### // COVACLEAN

- 🛨 CLEAN NEOPRENE STRAP
- OVERFLOW CHUTE FOR LIQUIDS
- **#** FITS OVER PRESCRIPTION SPECTACLES
- PVC FRAME / UPPER & LOWER INDIRECT VENTILATION
- 🛨 STERILISABLE BY GAMMA & BETA RADIATION



# **COVERALL CLEAN** & AUTOCLAVE

### FOR «CLEAN ROOMS»

MODEL	VERSIONS	REFERENCES	LENS MARKING	FRAME MARKING	COATINGS
COVERALL	Ventilated	COVACLEAN	2C-1,2 😭 1 BT €€	<b>≅</b> EN166 3 4 BT C€	ASAF
	Semi-ventilated	COVACLAVE	2C-1,2 😭 1 FT KN C€	₩ EN166 3 4 FT C€	Anti-scratch/Anti-fog (*P)

#### LENS MARKING

#### Optical class symbols:

Continuous work

#### Mechanical strength symbols:

- B. Medium energy impact, resists a 6 mm, 0.86 g ball at 120 m/s.
- F. Low energy impact, resists a 6 mm, 0.86 g ball at 45 m/s.
- T. The letter T, immediately after the mechanical strength symbol, authorises use for high speed particles at extreme temperatures.

- K. Resistance to surface damage by fine particles
- N. Resistance to fogging

#### TECHNOLOGY



The new exclusive scratch and fog resistant coating guarantees even more safety, reliability and comfort. Washable (water and soap), this permanent coating applied on both sides of the lens makes it highly scratch resistant and durably delays the appearance of fogging.

#### **PACKAGING AND EAN 13 CODE**

		COVACLEAN	COVACLAVE			
	Individual plaetic bag	3660740007850	3660740000646			
5 safety goggles per box		3660740107857	3660740100643			
	105 safety goggles per outer pack	3660740207854	3660740200640			









U.K. Bollé Safety

Surrey - KT9 2NY

Tél.: 00 44 (0)208 391 4700 Fax: 00 44 (0)208 391 4733

e-mail: sales@bolle-safety.co.uk

Unit C83 - Barwell Business Park Leatherhead Road - Chessington

Europe Bollé Safety 95 rue Louis Guérin 69100 Villeurbanne - France Tél.: 00 33 (0) 4 78 85 23 64

Fax: 00 33 (0) 4 78 85 28 56 contact@bolle-safety.com

bolle-safety.com

#### FRAME MARKING

EN 166: guaranteed minimum resistance of the protective eyewear against everyday risks including dropping the protective eyewear onto the ground, ageing by light exposure, exposure to heat or corrosion etc.

- 3. Liquid droplets or splashes.
- 4. Large dust particles > 5 microns.
- F. Low energy impact, resists a 6 mm, 0.86 g ball at 45 m/s.
- B. Medium energy impact, resists a 6 mm, 0.86 g ball at 120 m/s.
- T. The letter T, immediately after the mechanical strength symbol, authorises use for high speed particles at extreme temperatures.

Bollé Safety product approval certificates to CE standards will be sent on request.

#### CLEANING AND STORAGE

CLEANING: The lenses should be cleaned regularly. Bollé Safety recommends only using the B-clean lens cleaning system.

MAINTENANCE: Pitted, scratched or damaged lenses must be replaced by replacing the complete product. If the frame is damaged also replace the complete product. After each use it is recommended to keep the spectacles or goggles in a microfiber pouch or rigid case.

STORAGE: All products must be stored in a dry and clean environment.

#### CHARACTERISTICS

LENSES	PC - 2,2 mm - Curve 4	
FRAME	PVC (CLEAN) / TPR (CLAVE)	
TEMPLES	Non applicable	
STRAP	Adjustable - Isoprene	
FOAM	No	
MAINTENANCE AND CLEANING	Soapy water	
STERILIZATION COVACLAVE	121° / 20 mm / 15 Cycles	

06/12/2016

